

## Aspire Hand Made Pressure Reducing Seat



- Handmade pressure reducing seat
- Special foam design, engineered to improve the spread of pressure across the seat compliments users pressure management routine
- Waterproof but breathable anti-microbial four-way stretch Dartex material to optimises user comfort
- Independently tested and proven to be effective in reducing pressure levels
- Seat height: 65 mm

### Warranty Information

- 1 Year



✓ Contracted DVA product

✓ Contract approved

### Support @ Home

**Function:** Washing, bathing and showering

**Category:** Prescribed

Click [here](#) for more information

### NDIS

**Item Code:**

05\_093330084\_0103\_1\_2

**Mobile Shower Commode –**

**Composite:** 05\_413\_0103\_1\_2

Click [here](#) for more information

### Compliance

AS/NZS 3973:2009

| Code      | Display Name                            | Seat Depth | Seat Width |
|-----------|-----------------------------------------|------------|------------|
| BTC089122 | Pressure Reducing - Open Front - 320 mm | 320 mm     | 320 mm     |

| Code      | Display Name                                        | Seat Depth | Seat Width |
|-----------|-----------------------------------------------------|------------|------------|
| BTC089124 | Pressure Reducing - Closed Front - 320 mm           | 320 mm     | 320 mm     |
| BTC089126 | Pressure Reducing - Open Front - 400 mm             | 400 mm     | 400 mm     |
| BTC089128 | Pressure Reducing - Closed Front - 400 mm           | 400 mm     | 400 mm     |
| BTC089130 | Pressure Reducing - Open Front - 460 mm             | 460 mm     | 460 mm     |
| BTC089140 | Pressure Reducing - Closed Front - 460 mm           | 460 mm     | 460 mm     |
| BTC089150 | Pressure Reducing - Open Left - 460 mm              | 460 mm     | 460 mm     |
| BTC089160 | Pressure Reducing - Open Right - 460 mm             | 460 mm     | 460 mm     |
| BTC089170 | Pressure Reducing - Open Front - 500 mm             | 430 mm     | 500 mm     |
| BTC089180 | Pressure Reducing - Closed Front - 500 mm           | 430 mm     | 500 mm     |
| BTC089190 | Pressure Reducing - Open Front - 550 mm             | 460 mm     | 550 mm     |
| BTC089200 | Pressure Reducing - Closed Front - 550 mm           | 460 mm     | 550 mm     |
| BTC089210 | Pressure Reducing - Open Front - 600 mm             | 470 mm     | 600 mm     |
| BTC089220 | Pressure Reducing - Closed Front - 600 mm           | 470 mm     | 600 mm     |
| BTC089230 | Pressure Reducing - Open Front - 650 mm             | 480 mm     | 650 mm     |
| BTC089240 | Pressure Reducing - Closed Front - 650 mm           | 480 mm     | 650 mm     |
| BTC089250 | Pressure Reducing - Custom Size                     | -          | -          |
| BTC089131 | Pressure Reducing - Open Front - 460mm - Custom 4HC | -          | -          |